

CAPP

D E N M A R K



CAPP APS
LANDBRUGSVEJ 10
DK-5260 ODENSE
DENMARK

TEL. (+45) 6613 6140
FAX. (+45) 6613 2770

MAIL: INFO@CAPP.DK
WEB: WWW.CAPP.DK

Capp Controller

MOTORIZED PIPETTE CONTROLLER

- Light and fatigue free: weights only 167g, including the battery.
- Lithium battery with no memory effect and up to 12 hours of continuous use.
- Can be charged while using.
- Powerful: 50ml pipette is filled in less than 10 seconds.
- Express dispensing: depress the dispensing button past the built in point of resistance
- Gravity delivery and blow-out dispensing mode selection
- Fully adjustable speed-setting
- Exchangeable 0.2 μ m PTFE disc filter acts as effective shut-down system if overfill occurs.
- Silicon made exchangeable pipette holders.
- For use with glass or plastic pipettes ranging from 0.1ml to 100 ml.
- Vapour outlet for venting out corrosive liquids or fumes
- Fully autoclavable nose cone
- UV-resistant housing
- Complies with CE and RoHS



Ordering Info

Capp Motorized Controller

CAT. No.	DESCRIPTION
PA-100	Capp Motorized controller, 0.1-100ml